

E.P.I. CAT.2: **EN ISO 20345:2022** TALLAS: 36/48 (312/13) MONDOPOINT: 11 MADE IN: P.R.C

IMAGEN

ROTOR ESD S1PS SR FO HRO
 BTB0019B0K12


DESCRIPCION

Calzado de seguridad estilo running cumple con la nueva norma EN ISO 20345:2022.

Empeine en tejido Seamless 3D ultratranspirable. Refuerzos de TPU antiabrasión y detalles 3D en HF. Entre suela de EVA y suela inferior de goma. "FO+HRO". Ligera y deportiva, para realzar el dinamismo de quien las lleva.

CARACTERISTICAS

EMPEINE:

en tejido 3D Seamless, microperforado transpirable. Refuerzos de TPU antiabrasión y detalles 3D en HF.

REVESTIMIENTO INTERIOR:

Tejido 3D microperforado transpirable.

PLANTILLA EXTRAÍBLE:

antiestática en PU LD con termoformado ergonómico.

PLANTILLA ANTIPERFORACIÓN:

en fibra textil ultraligera "perforazione-zero" (PS - clavo Ø 3,0 mm).

PUNTERA:

en fibra de vidrio no magnética, aislante y resistente 200J.

SUELA ANTIDESLIZANTE y ANTIESTÁTICA:

super-comfortable EVA midsole, high energy absorption and FO+HRO nitrile rubber tread.

PLUS:

Sistema de bloqueo con rotor.

Refuerzos en Microfibra anti abrasión en la zona del talón. 100% libre de metal.

DETALLES



Logos y diseños decorativos realizados en sistema de **Micro inyección**. Detalles **3D en alta frecuencia** sobre los refuerzos en **TPU**.



SUELA



Perfiles segmentados para favorecer la flexión, a la vez que permite una gran evacuación de líquidos al caminar.

Paneles centrales diseñados para ofrecer un mayor agarre; proporcionan gran adherencia.

Perfiles segmentados que ayudan a la evacuación de líquidos y a un máximo Grip.

A - Slip resistance on ceramic tile floor with NaLS (forward heel 7°)	0,33 (≥0,31)
B - Slip resistance on ceramic tile floor with NaLS (backward forepart 7°)	0,36 (≥0,36)
C - Slip resistance on ceramic tile floor with glycerine (forward heel 7°)	0,27 (≥0,19)
D - Slip resistance on ceramic tile floor with glycerine (backward forepart 7°)	0,24 (≥0,22)

Suela intermedia en **EVA super confort**; proporciona un elevado nivel de absorción de la energía. Suela inferior en **Goma nitrílica**. Conforme **SR +FO +HRO**.

PLANTILLA INTERIOR EXTRAÍBLE



Plantilla extraíble, antiestática en **PU LD termoformado ergonómicamente**.

Fabricación totalmente **SEAMLESS**.

FICHA TECNICA



LANGUAGE	CODE	PAGE
ENGLISH	00	1
FRANCO	01	2
FRANCO	02	3
FRANCO	03	4
FRANCO	04	5
FRANCO	05	6
FRANCO	06	7
FRANCO	07	8
FRANCO	08	9
FRANCO	09	10
FRANCO	10	11
FRANCO	11	12
FRANCO	12	13
FRANCO	13	14
FRANCO	14	15
FRANCO	15	16
FRANCO	16	17
FRANCO	17	18
FRANCO	18	19
FRANCO	19	20
FRANCO	20	21
FRANCO	21	22
FRANCO	22	23
FRANCO	23	24
FRANCO	24	25
FRANCO	25	26
FRANCO	26	27
FRANCO	27	28
FRANCO	28	29
FRANCO	29	30
FRANCO	30	31
FRANCO	31	32
FRANCO	32	33
FRANCO	33	34
FRANCO	34	35
FRANCO	35	36
FRANCO	36	37
FRANCO	37	38
FRANCO	38	39
FRANCO	39	40
FRANCO	40	41
FRANCO	41	42
FRANCO	42	43
FRANCO	43	44
FRANCO	44	45
FRANCO	45	46
FRANCO	46	47
FRANCO	47	48
FRANCO	48	49
FRANCO	49	50
FRANCO	50	51
FRANCO	51	52
FRANCO	52	53
FRANCO	53	54
FRANCO	54	55
FRANCO	55	56
FRANCO	56	57
FRANCO	57	58
FRANCO	58	59
FRANCO	59	60
FRANCO	60	61
FRANCO	61	62
FRANCO	62	63
FRANCO	63	64
FRANCO	64	65
FRANCO	65	66
FRANCO	66	67
FRANCO	67	68
FRANCO	68	69
FRANCO	69	70
FRANCO	70	71
FRANCO	71	72
FRANCO	72	73
FRANCO	73	74
FRANCO	74	75
FRANCO	75	76
FRANCO	76	77
FRANCO	77	78
FRANCO	78	79
FRANCO	79	80
FRANCO	80	81
FRANCO	81	82
FRANCO	82	83
FRANCO	83	84
FRANCO	84	85
FRANCO	85	86
FRANCO	86	87
FRANCO	87	88
FRANCO	88	89
FRANCO	89	90
FRANCO	90	91
FRANCO	91	92
FRANCO	92	93
FRANCO	93	94
FRANCO	94	95
FRANCO	95	96
FRANCO	96	97
FRANCO	97	98
FRANCO	98	99
FRANCO	99	100

[illegible][illegible]

INSTRUCTION FOR USERS

PLEASE READ AND FOLLOW THESE INSTRUCTIONS

Before using the **WATERMETER**, please read this instruction. It is important that the technician, in highly detailed and responsible way, should follow the instructions in this manual. The instructions in this manual are intended to help you understand the operation of the device and to ensure that you use the device safely and effectively. Please read this instruction carefully and thoroughly before using the device. Please read this instruction carefully and thoroughly before using the device. Please read this instruction carefully and thoroughly before using the device.

SAFETY PRECAUTIONS

1. The device is not to be used in the presence of flammable or explosive gases or vapors. The device is not to be used in the presence of flammable or explosive gases or vapors. The device is not to be used in the presence of flammable or explosive gases or vapors.

INSTALLATION

1. The device should be installed in a dry, well-ventilated area. The device should be installed in a dry, well-ventilated area. The device should be installed in a dry, well-ventilated area.

OPERATION

1. The device should be operated in accordance with the instructions provided. The device should be operated in accordance with the instructions provided. The device should be operated in accordance with the instructions provided.

MAINTENANCE

1. The device should be maintained in accordance with the instructions provided. The device should be maintained in accordance with the instructions provided. The device should be maintained in accordance with the instructions provided.

WARRANTY

1. The device is warranted for a period of 12 months. The device is warranted for a period of 12 months. The device is warranted for a period of 12 months.


CONTACT INFORMATION

1. For more information, please contact our customer service department. For more information, please contact our customer service department. For more information, please contact our customer service department.



MANUAL DE USUARIO MULTIPLES IDIOMAS: (IT, EN, ES, DE, FR, BG, CS, ET, GR, HR, HU, LT, LV, NL, PL, PT, RO, SK, SL, SV)
Medidas: 120 x 165 mm

ETIQUETAS



Logo **TEAMWORK** estampado sobre la lengüeta. (15x60 mm).
Logo **ESD** sobre pasador de cordones.

ETOQUETA DE COMPOSICION:
Aplicada dentro del calzado derecho
Dim. 28 x 28mm

ETIQUETA CE INTERNA.
En el interior de la lengüeta.
Dim. 50 x 15mm

ETIQUETA TALLA:
Cosida entre el forro y la lengüeta.
Dim. 17x 14mm

PACKAGING



Caja de cartón SPARCO TEAMWORK azul / naranja con papel
tisú protector interno. Dimensiones caja: 343x258x123mm
Instrucciones de reciclaje válidas para ITALIA en la parte
inferior (PAP20).

ETIQUETA EXTERNA DE LA CAJA:

Aplicada en el lado designado de la caja, indica las características del producto, Certificado CE, número de lote, código de producto, código QR y código de barras.
Dim. 105x60 mm